

RotorFlow - RFI-Types, Visual Indicators

Applications - Visual only - RFI


There are varied applications, but some of the more common are:

- ▶ Plastic injection moulding equipment
- ▶ Visual flow on heat exchangers

Applications - Switch/Analogue Output - RFO & RFA


- | | |
|-----------------------------|-------------------------------|
| ▶ Lasers | ▶ Dispensing Systems |
| ▶ Medical Equipment | ▶ Chemical Metering Equipment |
| ▶ X-Ray Tubes | ▶ Water Sampling |
| ▶ Computers | ▶ Ice Making Machinery |
| ▶ Robotic Welding Equipment | ▶ Water Injection Systems |
| ▶ Water Purification/ | ▶ Proof of Delivery Systems |

Polypropylene Bodies



Adaptors, See Note 1

Metal Bodies



T	W	H	D	P
1/4	77	60	35	20
1/2	77	60	35	22
3/4	100	66	51	27
1	100	66	51	27

Notes:

1. Adaptors are supplied fitted to plastic units, sealed using Teflon (PTFE) tape.
2. If NPT thread is required for plastic units discard adaptor.
3. For pressure drop curves see RFS page.

OEMS

Specialist designs are available based on your requirements. Please contact Sales Office for further details on options such as potable water, enhanced chemical capabilities or 4-20mA loop powered units.

This is RotorFlow in its most basic form – a **BRIGHT ORANGE ROTOR** turning with fluid flow. Simple, direct and reliable.

Flow rate is estimated, or simply confirmed, by viewing the speed of the turning rotor. Either port may be used for incoming flow, and new bayonet mounting lens is easily removed for quick cleanout. RFI Type RotorFlow sensors are easy to see, easy to install and easy to afford.

Specifications

Wetted Materials	Polypropylene (Hydrolytically Stable, Glass Reinforced), SS or Brass
Body	
Rotor pin	Ceramic
Rotor	Moulded Nylon, Colour: High Visibility Orange
Lens	Polysulfone
O-Ring	Buna N (Metal body = Viton)
Adaptor	Acetal (Polypropylene body only)
Max. operating pressure	Polypropylene Body: 7 bar Metal Body: 14 bar
Max. operating temperature	Polypropylene Body: 80°C Metal Body: 100°C
Typical pressure drop	See Graph (Page 66)
Filtration	150 microns

How to Order

Body Material	Port Size	Flow Ranges (l/min)		Order Number	
		Low Range*	Standard Range	BSP	NPT
Polypropylene	1/4"	0.4 to 4.0	2.0 to 20.0	155420BSPP	155420
	1/2"	6.0 to 45.0	15.0 to 75.0	155480BSPP	155480
Brass	1/4"	0.4 to 4.0	2.0 to 20.0	142541BSPP	142541
	1/2"	6.0 to 45.0	15.0 to 75.0	142542BSPP	142542
	3/4"	---	20 to 112.5	180392BSPP	180392
	1"	---	30 to 225		181681
Stainless Steel	9/16 x 18 UNF	0.4 to 4.0	2.0 to 20.0	N/A	174596
	1/2"	6 to 45	15.0 to 75.0	173138BSPP	173138
	3/4"	---	20 to 112.5	181682BSPP	181682
	1"	---	30 to 225		181683

* With use of low flow adaptor supplied